



Wattstopper
DLM Wireless 1-Button Dimming Wall Switch, Lt. Almond
Part No. LMDM-601-LA



The LMDM-601 Dimming Wall Switch is a wireless low voltage device for dimming control of one or more lighting loads. It is part of the NEW wireless Digital Lighting Management (DLM) system and can dim load(s) connected to wireless DLM dimming room controllers (LMRC-611) for a totally wireless room. Alternatively it can be used in a hybrid wired & wireless room to control loads connected to a traditional wired room controller (e.g. LMRC-111) when used in conjunction with a wireless bridge (LMBC-650).

Features & Benefits

Wireless 1-Button Dimming Wall Switch

The LMDM-601 Dimming Wall Switch is a wireless low voltage device for dimming control of one or more lighting loads. It is part of the NEW wireless Digital Lighting Management (DLM) system and can dim load(s) connected to wireless DLM dimming room controllers (LMRC-611) for a totally wireless room. Alternatively it can be used in a hybrid wired & wireless room to control loads connected to a traditional wired room controller (e.g. LMRC-111) when used in conjunction with a wireless bridge (LMBC-650).

Built-in IPv6 Mesh and Bluetooth antennas provide robust signal strength and reliable communication

Uses IPv6 Mesh to establish network communication with all DLM wireless devices

Low voltage switch with LED status indicator for control of dimmable loads

Quick and easy wireless installation – no Cat 5e connection needed

Ground wire allows you to install next to a line voltage device. This wire is only needed when placed next to a line voltage device in the same box. Grounding cables are otherwise not needed if in a purely low voltage application.

10+ year battery life, with LED indicator for low battery alert- battery level can be viewed with wireless DLM software

Specifications

General Info

Product Line	Wattstopper	Color	Light Almond
UPC Number	754182944316	Country Of Origin	China
Features	Wireless		

Technical Information

Amperage	1.5 A	Wattage	4.5 W
Voltage	3 V		
