



**Wattstopper**  
**Discontinued - Digital Switch, 2-button w/infrared, Light Almond**  
 Part No. LMSW-102-LA



LMSW-100 Series Wall Switches are low voltage devices for energy-saving manual on/off control of one or more loads from one or more locations. They are part of a Digital Lighting Management (DLM) system and can control any load(s) connected to DLM room controllers.

## Features & Benefits

- Low voltage pushbutton switches for control of multiple loads
- Components of Digital Lighting Management integrated control system
- Plug to other components using Cat 5e cables with RJ45 connectors eliminating wiring errors
- Customizable buttons with LED status indicators
- IR transceiver for wireless configuration and remote control
- Plug n' Go automatic configuration and Push n' Learn for personalization

## Specifications

### General Info

Product Line	Wattstopper	Color	Light Almond
Finish	Glossy	UPC Number	754182925469
Country Of Origin	China	Product Series	LMSW
Switch Type	Push	Number of Switches	2
Application Sector	Commercial	Standard	UL, cUL, FCC part 15, RoHS
Warranty Type	5-Year	Type	Switch

### Dimensions

Product Width US	1.8 in	Product Weight US	0.2 lb
Product Volume US	20.3 cu in	Product Depth US	1.6 in

---

Product Height US	4.1 in
-------------------	--------

---

### Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

### Technical Information

---

Operating Temperature Min	0 °C	Compatibility	DLM Wired
---------------------------	------	---------------	-----------

---

Has Battery	No	Operating Temperature Max	55 °C
-------------	----	---------------------------	-------

---

Number of Buttons	2	Number of Rockers	0
-------------------	---	-------------------	---

---

Topology	Free Topology	Input Voltage	24 VDC
----------	---------------	---------------	--------

---

Indoor/Outdoor	Indoor	Mounting Type	J-Box
----------------	--------	---------------	-------

---

Current Draw	5 mA	Operating Temperature	0°-55°C, 32°-131°F
--------------	------	-----------------------	--------------------

---

Operating Humidity	5-95% RH (Non-Condensing)	Wire Connection Type	RJ-45
--------------------	---------------------------	----------------------	-------

---

Engraving Type	Blank	Storage Temperature	23° - 176° F, -5° - 80° C
----------------	-------	---------------------	---------------------------

---