



Wattstopper
DLM Single Relay Room Controller, On/Off, 120-277V, USA
Part No. LMRC-102-U



LMRC-100 Series Digital Room Controllers include one or two relay(s) for on/off control of a total of 20 amps, and a highefficiency switching power supply. They are the foundation of a Wattstopper Digital Lighting Management (DLM) system, and allow integration of occupancy sensors, daylighting sensors and switches for energy-efficient lighting control.

Features & Benefits

Plenum-rated controllers with line voltage relay(s) and switching power supply

Components of Digital Lighting Management integrated control systems

Plug to other components using Cat 5e cables with RJ45 connectors eliminating wiring errors

Plug n' Go automatic configuration for maximum energy efficiency

Support energy saving manual-on and bi-level lighting control strategies

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182930944
Country Of Origin	United States	Product Series	LMRC
Installation Location	Ceiling	Application Sector	Commercial
Standard	UL 2043, cUL, FCC part 15, PEP, ISO 14025:2010, ISO 14001, RoHS 2011/65/EC, BAA, TAA	Warranty Type	5-Year
Type	Room Controller		

Dimensions

Product Width US	4.4 in	Product Weight US	0.62 lb
Product Volume US	44.6 cu in	Product Depth US	1.9 in
Product Height US	3.9 in		

Technical Information

Operating Temperature Min	32 °F	Output Voltage	24 VDC
Load Rating	20 A @ 120/230/240/277 VAC	Compatibility	DLM Wired
Has Battery	No	Number of Connections	3
Dimming Compatibility	On/Off	Operating Temperature Max	104 °F
Topology	Free Topology	Number of Relays	1
Input Voltage	120/230/240/277 VAC	Line Frequency	50 Hz, 60 Hz
Indoor/Outdoor	Indoor	Mounting Type	1/2 in Knockout, 4 in J-Box
Current Draw	20 A	Operating Temperature	0°-40°C, 32°- 104°F
Operating Humidity	5-95% RH (Non-Condensing)	Wire Connection Type	RJ-45
Storage Temperature	23° - 176° F		
