



Wattstopper
Discontinued - Digital Scene Switch, 5-button w/IR, Lt. Almond
Part No. LMSW-105-LA



LMSW-100 Series Wall Switches are low voltage devices for energy-saving manual on/off control of one or more loads from one or more locations. They are part of a Digital Lighting Management (DLM) system and can control any load(s) connected to DLM room controllers.

Features & Benefits

| | |
|---|--|
| Low voltage pushbutton switches for control of multiple loads | Components of Digital Lighting Management integrated control system |
| Plug to other components using Cat 5e cables with RJ45 connectors eliminating wiring errors | Customizable buttons with LED status indicators |
| IR transceiver for wireless configuration and remote control | Plug n' Go automatic configuration and Push n' Learn for personalization |

Specifications

General Info

| | | | |
|--------------------|-------------|--------------------|----------------------------|
| Product Line | Wattstopper | Color | Light Almond |
| Finish | Glossy | UPC Number | 754182929290 |
| Country Of Origin | China | Product Series | LMSW |
| Switch Type | Push | Number of Switches | 5 |
| Application Sector | Commercial | Standard | UL, cUL, FCC part 15, RoHS |
| Warranty Type | 5-Year | Type | Switch |

Dimensions

| | | | |
|-------------------|------------|-------------------|--------|
| Product Width US | 1.8 in | Product Weight US | 0.2 lb |
| Product Volume US | 20.3 cu in | Product Depth US | 1.6 in |
| Product Height US | 4.1 in | | |

Additional Information

RoHS Compliant Yes

Technical Information

| | | | |
|---------------------------|---------------------------|---------------------------|---------------------------|
| Operating Temperature Min | 0 °C | Compatibility | DLM Wired |
| Has Battery | No | Operating Temperature Max | 55 °C |
| Number of Buttons | 5 | Number of Rockers | 0 |
| Topology | Free Topology | Input Voltage | 24 VDC |
| Indoor/Outdoor | Indoor | Mounting Type | J-Box |
| Current Draw | 5 mA | Operating Temperature | 0°-55°C, 32°-131°F |
| Operating Humidity | 5-95% RH (Non-Condensing) | Wire Connection Type | RJ-45 |
| Engraving Type | Blank | Storage Temperature | 23° - 176° F, -5° - 80° C |