



Wattstopper
DLM Room Controller, 1 Relay, 0-10V Dimming, 347V
Part No. LMRC-211-347



LMRC-210 Series Digital Room Controllers include one, two or three relay(s) to switch a total of 15 or 20 amps, a high efficiency switching power supply and one 0-10 volt output per relay for control of dimmable loads including electronic ballasts (Advance Mark 7, or equivalent). They are the foundation of a Wattstopper Digital Lighting Management (DLM) system, and allow integration of occupancy sensors, daylighting controls and switches for energy-efficient lighting control.

Features & Benefits

Plenum-rated controllers with line voltage relay(s) and 0-10 volt dimming output(s)	120/230/240/277 volt and 347 volt models
Plug to other components using Cat 5e cables with RJ45 connectors eliminating wiring errors	Plug n' Go automatic configuration for maximum energy efficiency
Store load preset level and 16 scene preset levels for each load	Support energy saving manual-on, bi-level, tri-level and dimming control strategies

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182928934
Country Of Origin	China	Product Series	LMRC
Installation Location	Ceiling	Application Sector	Commercial
Standard	UL 924, UL 60730, UL 2043, cUL, FCC part 15, PEP, RoHS 2011/65/EC, ISO 14025:2010, ISO 14001, ISO 14040:2006, ISO 14044:2006	Warranty Type	5-Year
Type	Room Controller		

Dimensions

Product Width US	6.5 in	Product Volume US	226.0 cu in
Product Depth US	3.3 in	Product Height US	6.5 in

Additional Information

RoHS Compliant Yes

Technical Information

Operating Temperature Min 32 °F Output Voltage 24 VDC

Compatibility DLM Wired Has Battery No

Number of Connections 7 Dimming Compatibility 0-10 V

Operating Temperature Max 140 °F Topology Free Topology

Number of Relays 1 Input Voltage 347 VAC

Line Frequency 50 Hz, 60 Hz Indoor/Outdoor Indoor

Mounting Type 4 in Deep J-Box Current Draw 15 A

Operating Temperature 0°-60°C, 32°-140°F Operating Humidity 5-95% RH
(Non-Condensing)

Wire Connection Type RJ-45, Terminal Block Storage Temperature 23° - 176° F
