



Pass and Seymour
LS Series CFL/LED/Incandescent Single Pole Slide Dimmer, Non-Preset, Brown
Part No. LSCL450



Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

Features & Benefits

CFL/LED dimmable bulb compatible (except for 0-10V LED drivers)

Works with dimmable CFL/LED or Incandescent lighting loads at 450W CFL/LED & 700W Incandescent

Built-in electromagnetic and radio-frequency interference protection

No dirt-catching crevices

Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plates available for all models

Preset ON/OFF switch automatically returns controlled lights to preset level without re-adjusting dimmer setting

Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts

Superior heat management

Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer

Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	UPC Number	785007040494
Country Of Origin	China	Features	Low-End Trim (Dim Range)
Switch Type	Single Pole, Slider	Number of Switches	1
Application Sector	Residential	Standard	cULus, RoHS

Warranty Type	Limited Lifetime Warranty	Type	Dimmer
Dimensions			
Product Width US	1.74 in	Product Depth US	1.28 in
Product Height US	4.19 in		
Technical Information			
Preset	No	Load Rating	120V 4.5A 450W (CFL), 120V 4.5A 450W (LED), 120V 700W (Halogen), 120V 700W (Incandescent)
Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
Number of Gangs	1	Minimum Load Recommendation	10 W
Bulb Compatibility	CFL, Halogen, Incandescent, LED	Number of Poles	Single Pole
Wire Size	#14 - #10 AWG	Trim/Adjustment Level	Wheel
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Screw Terminals
Voltage	120 VAC	Environmental Conditions	Humidity: Less than 95% non condensing