



Wattstopper
Discontinued - DLM Pre-Eng Color Control Timer Switch, Black
Part No. LMTS-101-CCT-B-ENG1



The LMTS-101-CCT from Wattstopper allows building occupants to enjoy the benefits of Human Centric Lighting by automatically adjusting Correlated Color Temperature (CCT) on a scheduled cycle throughout the day. It can make any building environment feel more visually comfortable by automatically replicating the inviting feeling of natural daylight, but is especially well-suited for commercial offices, healthcare, and educational facilities. The interface is designed to work with light fixtures that are enabled for tunable white with Blanco and Araya logic modules (also from Wattstopper). Notes: Switches do not include face plates. Order decorator style plate separately.

Features & Benefits

Low Voltage CCT Timer Switch	The LMTS-101-CCT from Wattstopper allows building occupants to enjoy the benefits of Human Centric Lighting by automatically adjusting Correlated Color Temperature (CCT) on a scheduled cycle throughout the day. It can make any building environment feel more visually comfortable by automatically replicating the inviting feeling of natural daylight, but is especially well-suited for commercial offices, healthcare, and educational facilities. The interface is designed to work with light fixtures that are enabled for tunable white with Blanco and Araya logic modules (also from Wattstopper). Notes: Switches do not include face plates. Order decorator style plate separately.
Sleek single gang device fits decorator wall plates	Programming buttons hidden behind override button
Low-profile styling with the choice of five decorator colors and compatible with decorator wall plates	High resolution screen for all schedule entries
LED indicator for visibility in darkened rooms	Programmable button to manually control connected load or override the schedule

Specifications

General Info

Product Line	Wattstopper	Color	Black
UPC Number	754182946655	Country Of Origin	China

Application Sector	Commercial	Standard	UL
Type	Combination		