



Q-Series OFP Standard Density Adapter Panels offer pass-through connections and front-loading access for Q-Series Enclosures. Compatible with Q-Series Rack Mount or Wall Mount Fiber Enclosures.

Features & Benefits

Multiple Color options available: Red, Green, Beige, Aqua Fiber port labeling: Provides fiber port identification for easier administration

Plunger/grommet fasteners: Quick and easy insertion and removal

Specifications

General Info

Product Line	Ortronics	Color	Gray
Country Of Origin	Mexico	Material	Steel
Features	Toolless Installation	Included	Cover
Application Sector	Commercial, Data Center	Standard	RoHS compliant. Meets or exceeds TIA/EIA-568-C.3 requirements.
Warranty Type	5-Year	Type	Adapter Panel

Dimensions

Product Width US	5.12 in	Product Depth US	0.78 in
Product Height US	1.19 in		

Technical Information

Fiber Optic Cable Type	OM3, OM4, OS2	Operating Temperature Min	-10 °C
Compatibility	OFP	Number of Ports	72
Alignment Sleeve Material	Zirconia	Simplex/Duplex	Duplex
Polarity Type	Universal	Operating Temperature Max	60 °C
Single/Multimode	Multimode/Single-mode	Number of Fibers	72
Connector 2	MPO Female	Connector 1	MPO Female
Operating Temperature	-10°-60°C	Durability	500 matings
Operating Humidity	0-80% RH (Non-Condensing)	Connectivity Footprint	Q-Series Standard Density
Storage Temperature	-40° - 75° C		
