



Ortronics
Q-Series OFP Adapter Panel 6 SC-Duplex aqua
Part No. OFP-SCD12LC



Ortronics fiber adapter panel allows for flexibility and expansion with an industry accepted style. The adapter panel snaps in for installation and can be removed easily for future changes. The adapter panel is silkscreened for easy port identification.

Features & Benefits

Small footprint: Up to 72 LC fibers per RU

Adapter panels available with a wide variety of configurations: Available in, LC, SC, ST and blank styles

Plunger/grommet fasteners: Made of durable polycarbonate

Front loading: Zirconia ceramic sleeves for optimal performance

Fiber port labeling: 6, 8, 12 & 24 port panels

Engineered polymer adapter panel: Color options available

Utilizes Shuttered Adapters

Specifications

General Info

Product Line	Ortronics	Color	Aqua
UPC Number	662875629177	Country Of Origin	Mexico
Material	Thermoplastic	Product Type	Adapter Panel
Features	Toolless Installation	Included	Cover
Application Sector	Commercial, Data Center	Standard	RoHS compliant. Meets or exceeds TIA/EIA-568-C.3 requirements.
Warranty Type	5-Year		

Dimensions

Product Width US	5.12 in	Product Depth US	1.43 in
Product Height US	1.19 in		

Technical Information

Fiber Optic Cable Type	OS2	Operating Temperature Min	-10 °C
Compatibility	Q-Series SD Enclosure, RFP SD Panels	Number of Ports	12
Alignment Sleeve Material	Zirconia	Simplex/Duplex	Duplex
Operating Temperature Max	60 °C	Shuttered Adapters	No
Single/Multimode	Multimode	Number of Fibers	12
Connector 2	SC Female	Connector 1	SC Female
Form Factor	SC Duplex	Operating Temperature	-10°-60°C
Durability	500 matings	Operating Humidity	0-80% RH (Non-Condensing)
Connectivity Footprint	Q-Series Standard Density	Storage Temperature	-40° - 75° C