



Pass and Seymour

High Strength with Flexible Eye
Part No. MSP125

High Strength with Flexible Eye, Single-Double-Triple Weave. Cable Diameter - 1.250-1.490", Mesh Length -56", Break Strength - 30,600 lbs.



Features & Benefits

High strength pulling grips are designed for situations where loads and safety considerations require an extra high strength grip.

They are most commonly used for attaching pulling lines to conductors, conductors to running boards and conductor-to-conductor connections.

These grips can be used for pulling bare or insulated conductor, wire rope or synthetic rope.

Specifications

General Info

UPC Number	785007999181	Country Of Origin	Mexico
Product Line	Pass & Seymour	Application Sector	Industrial
Construction	Various Types of Pulling, Support and Strain Relief Grips	Standard	UL/CSA Approval (consult factory)

Technical Information

Mounting	Consult the Factory for Mounting Recommendations	Cable Size	Cable Dia. Range: 1.250-1.490; Mesh Length: 56
Capacity	Various Cable Diameter Ranges	Load	Approx. Break Strength: 30,600