



Wiremold  
Wiremold OFR Series Overfloor Raceway Entrance End Fitting  
Part No. OFR10A

Wiremold OFR Series Overfloor Raceway System provides four-channels of capacity and access to a wide range of power, communications, and A/V connectivity options in the smallest, lowest, narrowest, ADA compliant profile available in overfloor raceway systems. This system installs over existing floor coverings and is both tamper-resistant and installer-friendly, making it an ideal solution for relocatable or permanent installations where access through floors and ceilings is not an option.

## Features & Benefits

This product meets the material restrictions of RoHS

## Specifications

### General Info

|                    |              |                   |  |
|--------------------|--------------|-------------------|--|
| Product Line       | Wiremold     | Color             | Black  |
| UPC Number         | 786776175158 | Country Of Origin | Mexico   |
| Application Sector | Commercial   | Standard          | cETLus Listed Surface Metal Raceway: Report Number G100217061CRT-001 |
| Type               | Raceway      |                   |  |

### Dimensions

|                   |             |                   |        |
|-------------------|-------------|-------------------|--------|
| Product Width US  | 4.75 in     | Product Weight US | 3.0 lb |
| Product Volume US | 83.13 cu in | Product Depth US  | 7.0 in |
| Product Height US | 2.5 in      |                   |        |

### Listing Agencies / 3rd Party Agencies

|            |     |                   |                   |
|------------|-----|-------------------|-------------------|
| ETL Listed | Yes | ETL ListingNumber | G100217061CRT-001 |
|------------|-----|-------------------|-------------------|

### Additional Information

|                |     |                               |     |
|----------------|-----|-------------------------------|-----|
| RoHS Compliant | Yes | Product Environmental Profile | Yes |
|----------------|-----|-------------------------------|-----|

---

Technical Information

---

|         |         |
|---------|---------|
| Voltage | 300.0 V |
|---------|---------|

---