



Wattstopper
8 port Ethernet switch for LSM, DIN mounting
Part No. NB-SWITCH-8



The NB-SWITCHES are enterprise-grade Ethernet switches that work with up to four or seven NB-ROUTERS to provide high speed connectivity for Digital Lighting Management (DLM) networked systems. The compact switch has a rugged metal enclosure and integral DIN rail clip.

Features & Benefits

100 Mbps 5-port, 8-port and 16-port Ethernet switches

10BASE-T/100BASE-TX/ 100BASE-T operation

Auto negotiation of speed and duplex

Compatible with DLM Segment Manager or third party BACnet building automation systems

Specifications

General Info

Product Line	Wattstopper	Color	Gray
Finish	Painted	UPC Number	754182933945
Country Of Origin	United States	Product Series	NB
Features	Unmanaged Switch	Installation Location	Enclosure, Wall
Application Sector	Commercial	Standard	IP30, RoHS, UL 508
Warranty Type	1-Year	Type	Network Switch

Dimensions

Product Width US	2.74 in	Product Weight US	1.5 lb
Product Height US	2.0 in	Product Length US	3.94 in

Technical Information

Operating Temperature Min	32 °F	Compatibility	DLM Wired
Number of Connections	8	Power Supply	10-36 VDC, 24 VAC

Operating Temperature Max	140 °F	Data Transfer Rate	100 Mbps
Indicator	Network Status LED, Power LED	Connector Type	RJ-45
Input Voltage	24 VDC/VAC	Indoor/Outdoor	Indoor
Mounting Type	DIN Rail	Operating Temperature	0°-60°C, 32°-140°F
Operating Humidity	10-95% RH (Non-Condensing)	Storage Temperature	-40° - 85° C