



**Legrand**  
**P300 Player Preamplifier**  
Part No. NVP300NA

The Nuvo NV-P300-XX Player Preamplifier is a versatile addition to the Player Portfolio, ideal for introducing incredible source flexibility and superior audio to maximize an external power amplifier's capabilities. Check out the Player Portfolio mobile app. Outside North America? Use -EU, -UK or -AU when ordering.



## Features & Benefits

All your favorite music is right at your fingertips with easy access to networked computers, streaming Internet Radio, and even audio content stored on an Android or iOS device.

Supports both wired Ethernet and wireless 802.11n configuration options adding flexibility for any home.

Connect to storage devices, analog equipment, or home theater receivers through the unit's audio line-in, line-out, MiniTOSLINK fiber optic digital input and output, or USB ports.

Attractive contemporary industrial design discreetly fits into small spaces.

Seamless integration into advanced automation systems from Vantage, Crestron, Control4, KNX, and more - visit the Player Portfolio third party drivers page. \*Streaming services subject to geographic availability. Service subscriptions may be required.

Compatible with Legrand's other Nuvo Player Portfolio products for a truly custom, easily expandable system (up to sixteen zones).

Includes 802.11n wireless capability and utilizes both 2.4 and 5 Ghz bands, for fast signals and broad coverage.

Manage your music via the convenient wall-mounted P10 keypad or wirelessly from the palm of your hand with free apps for your Apple or Android device.

Remote network and device management with Domotz PRO

## Specifications

### General Info

UPC Number	701963855293
Country Of Origin	China
Product Line	Nuvo
Included	P300 Player, Power Cord, and Quick Start Guide
Application Sector	Residential
Standard	FCC, IC, CE-EMC, C-Tick, cTUVus, CE-LVD, RoHS

### Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

### Technical Information

Wattage	5.1 W
---------	-------

---

**Input**

RJ45, TOSLINK/mini-TOSLINK, USB (Type A)

---