



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

Features & Benefits

Material: Aluminum Alloy 6063-T6

Finish: Plain

Bottom: Ldr: 1" wide I rung SB: Flat Sheet over 12" Rung Spacing.
SC: Solid Corrugated VC: Vented Corrugated

Construction: Welded

Tray Design: Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126.

Tray Grounding Capability: Classified as an equipment grounding conductor per NEC 392.60.

Specifications

General Info

| | | | |
|--------------|-------------------|--------------------|------------------------|
| Product Line | Cablofil | Finish | Aluminum |
| UPC Number | 800388059726 | Country Of Origin | Mexico |
| Bottom Type | Ladder | Application Sector | Commercial, Industrial |
| Type | Straight Sections | | |

Dimensions

| | | | |
|-------------------|-----------|-------------------|----------|
| Product Width US | 6.0 in | Product Weight US | 19.2 lb |
| Product Volume US | 2.0 cu ft | Product Depth US | 144.0 in |
| Product Height US | 4.0 in | Rung Spacing | 6 in |

Trade Programs

| | |
|-----|-----|
| BAA | Yes |
|-----|-----|

Technical Information

| | |
|-----------------|-----|
| NEMA Load Class | 12C |
|-----------------|-----|