



Cablofil
SB-4A12B-S120-06 AL 4H SOLBOT 120L 06W
Part No. P300086



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

Features & Benefits

Material: Aluminum Alloy 6063-T6

Finish: Plain

Bottom: Ldr: 1" wide I rung SB: Flat Sheet over 12" Rung Spacing.
SC: Solid Corrugated VC: Vented Corrugated

Construction: Welded

Tray Design: Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126.

Tray Grounding Capability: Classified as an equipment grounding conductor per NEC 392.60.

Specifications

General Info

Product Line	Cablofil	Finish	AL
UPC Number	800388059511	Country Of Origin	Mexico

Dimensions

Product Width US	7.5 in	Product Weight US	16.987 lb
Product Volume US	2.151 cu ft	Product Depth US	120.0 in
Product Height US	4.13 in		

Buy American Act Compliance

BAA	Yes
-----	-----