



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

## Features & Benefits

Material: Aluminum Alloy 6063-T6

Finish: Plain

Bottom: Ldr: 1" wide I rung SB: Flat Sheet over 12" Rung Spacing.  
SC:Solid Corrugated VC: Vented Corrugated

Construction: Welded

Tray Design: Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126.

Tray Grounding Capability: Classified as an equipment grounding conductor per NEC 392.60.

## Specifications

### General Info

Product Line	Cablofil	Finish	Aluminum
UPC Number	800388062917	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Type	Cable Tray

### Dimensions

Product Width US	7.5 in	Product Weight US	29.46 lb
Product Volume US	2.656 cu ft	Product Depth US	144.0 in
Product Height US	4.25 in		

### Trade Programs

BAA	Yes
-----	-----