



Pass and Seymour
PIR Multi-Way Single-Relay Wall Mounted Occupancy Sensor, 800W at 120V/1200W at 277V, White
Part No. WPS10W



The WPS10 passive infrared (PIR) wall switch sensor can turn lights OFF and ON based on occupancy.

Features & Benefits

- Color-matched lens and low profile for appealing design
- Optional neutral connection with break off tab to expose neutral terminals
- 120/240/277 VAC and 347 VAC models
- Allows multi-way control from one of up to four control locations
- High sensitivity and dense coverage for exceptional performance
- Defaults to Manual-ON operation for maximum energy savings

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Gloss	UPC Number	785007501773
Country Of Origin	China	Material	ABS
Product Series	PW-300	Features	Adjustable Time Delay, Indicator Lights, Light Level Sensor, Sensitivity Adjustment, Vandal Resistant Lens
Switch Type	Motion Sensor	Installation Location	Wall
Application Sector	Commercial	Warranty Type	5-Year
Type	Occupancy Sensor		

Dimensions

Product Width US	1.75 in	Product Depth US	1.81 in
Product Height US	2.73 in	Product Length US	2.73 in

Additional Information

Product Has Potential to Contribute to LEED	Yes	Energy Savings	Yes
---	-----	----------------	-----

Technical Information

Operating Temperature Min	32 °F	Load Rating	1000 W @ 120 VAC, 1200 W @ 240/277 VAC
Sensor Coverage Pattern	180 °	Sensor Type	Occupancy
Frequency Band	60 Hz	Operating Temperature Max	131 °F
Light Level Adjustment	8-180 fc	Number of Buttons	1
Sensor Technology	Passive Infrared (PIR)	Timer Duration	5-30 Minutes
Number of Poles	Multi-Location	Indicator	PIR Detection LED
Input Voltage	120/240/277 VAC	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Sensitivity Adjustment	PIR (Min/Max)
Mounting Type	In-Wall	On Function	Selectable Auto/Manual
Operating Temperature	0°-55°C, 32°-131°F	Operating Humidity	5-95% RH (Non-Condensing)
Sensing Range	Major motion 35 x 30 ft, Minor motion 20 x 15 ft	Location Rating	Dry
Wire Connection Type	Flying Leads	Storage Temperature	23° - 176° F, -5° - 80° C