



Pass and Seymour
Multi-Way Passive Infrared Single-Relay 0-10V Dimming Wall Mounted Occupancy Sensor, White
Part No. WPSD10W



The WPSD10W passive infrared (PIR) dimming wall switch sensor can turn lights OFF and ON based on occupancy

Features & Benefits

Optional Smart Light Level adapts ambient light hold off threshold to meet user needs	Selectable walk-through mode turns lights off three minutes after the room is initially occupied if no motion is detected after the first 30 seconds
Test mode allows quick and easy verification of coverage	Selectable audible and/or visual alerts for impending shutoff
LED indicates occupancy detection	Vandal resistant lens combines precise coverage with durability
Presentation mode may be deactivated to allow Auto-ON operation after 15 second time delay	

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Gloss	UPC Number	785007501780
Country Of Origin	China	Material	ABS
Product Series	PW-310	Features	Adjustable Time Delay, Dimming, Indicator Lights, Light Level Sensor, Sensitivity Adjustment, Vandal Resistant Lens

Switch Type	Motion Sensor	Installation Location	Wall
Application Sector	Commercial	Warranty Type	5-Year
Type	Occupancy Sensor		
Dimensions			
Product Width US	1.75 in	Product Depth US	1.81 in
Product Height US	2.73 in	Product Length US	2.73 in
Additional Information			
Product Has Potential to Contribute to LEED	Yes	Energy Savings	Yes
Technical Information			
Operating Temperature Min	32 °F	Load Rating	1000 W @ 120 VAC, 1200 W @ 240/277 VAC
Sensor Coverage Pattern	180 °	Sensor Type	Occupancy
Frequency Band	60 Hz	Operating Temperature Max	131 °F
Light Level Adjustment	8-180 fc	Number of Buttons	3
Sensor Technology	Passive Infrared (PIR)	Timer Duration	5-30 Minutes
Number of Poles	Multi-Location	Indicator	PIR Detection LED
Input Voltage	120/230/240/277 VAC	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Sensitivity Adjustment	PIR (Min/Max)
Mounting Type	In-Wall	On Function	Selectable Auto/Manual
Operating Temperature	0°-55°C, 32°-131°F	Operating Humidity	5-95% RH (Non-Condensing)

Sensing Range	Major motion 35 x 30 ft, Minor motion 20 x 15 ft	Location Rating	Dry
Wire Connection Type	Flying Leads	Storage Temperature	23° - 176° F, -5° - 80° C