



Pass and Seymour
24 VDC Universal Voltage Power Pack, Auto On/Off
Part No. PBZ50

Provides 24 VDC operating voltage to 's low-voltage occupancy sensors.



Features & Benefits

LED indicates status of relay or if there is a low-voltage overcurrent	The product meets the materials restrictions of RoHS
Zero crossing circuitry for reliability and increased product life	UL 2043 plenum rated for cost-effective installation
1/2" snap-in nipple attaches to standard electrical enclosures through 1/2" knockouts	Self-contained power supply relay system
Efficient switching power supply providing optimized current output based on number of sensors	

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007501667	Country Of Origin	China
Material	Plastic	Product Series	BZ
Features	Load Shed Capability	Installation Location	Ceiling
Application Sector	Commercial	Warranty Type	5-Year
Type	Power Pack		

Dimensions

Product Width US	1.673 in	Product Depth US	1.634 in
Product Length US	2.916 in		

Additional Information

Product Has Potential to Contribute to LEED	Yes	Energy Savings	Yes
---	-----	----------------	-----

Technical Information

Operating Temperature Min	33 °F	Operating Temperature Max	105 °F
Indicator	LED Light	Input Voltage	120/277 VAC, 230/240 VAC
Indoor/Outdoor	Indoor	Mounting Type	Fixture Wiring Tray, J-Box
On Function	Selectable Auto/Manual	Operating Temperature	32°-104°F
Operating Humidity	5-95% RH (Non- Condensing)	Wire Connection Type	Wire Leads