



Pass and Seymour  
Industrial Extra Heavy Duty Specification Grade Switch, Gray  
Part No. PS20AC3GRY

3-Way Toggle Switch, Back and Side-Wire, 20A 120/277V



## Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

Oversized silver-alloy contacts for long life and better heat dissipation.

Heavy-duty, brass alloy, one-piece contact arm virtually eliminates contact bounce.

Shallow design for easier installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Impact- and chemical-resistant cover.

One-piece nickel-plated brass strap for superior corrosion-resistance.

Cam control and spring actuator for positive "makes and breaks."

Locking support provides resistance to face and back body separation.

Side and external screw-pressure-plate back wire with #14 - #10 AWG copper or copper-clad wire.

Grounding terminal is standard with screw-pressure plate back wire.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007195392
Country Of Origin	Mexico	Application Sector	Industrial

Standard

UL20, FEDSPEC

Dimensions

Product Width US	1.25 in	Product Depth US	1.09 in
Product Height US	4.195 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Contact Rating	20 Amp, 120/277 VAC	Amperage	20 A
Number of Poles	3-Way	Wire Size	#14 - #10 AWG