



Pass and Seymour
Multi-Way Dual Technology Occupancy Sensor, Single-Relay, 120/277V, Ivory
Part No. WDS10I



The WDS10 dual technology wall switch sensor turns lights OFF and ON based on occupancy.

Features & Benefits

- Selectable walk-through mode turns lights off three minutes after initial occupancy if no motion is detected after the first 30 seconds
- Test mode allows quick and easy adjustments
- Selectable audible alert for impending shutoff
- In automatic mode, sensor returns automatically to Auto-ON after lights are turned off manually
- ideal for presentations
- Four occupancy logic options to customize control to meet application needs
- Zero-crossing for long relay life

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Gloss	UPC Number	785007501698
Country Of Origin	China	Material	ABS
Product Series	DSW-301	Features	Adjustable Time Delay, Indicator Lights, Light Level Sensor, Sensitivity Adjustment, Test Mode, Walkthrough Mode

Switch Type	Motion Sensor, Push	Installation Location	Wall
Application Sector	Commercial	Warranty Type	5-Year
Type	Occupancy Sensor		
Dimensions			
Product Width US	1.76 in	Product Depth US	1.83 in
Product Height US	2.73 in	Product Length US	2.73 in
Additional Information			
Product Has Potential to Contribute to LEED	Yes	Energy Savings	Yes
Technical Information			
Operating Temperature Min	32 °F	Load Rating	1000 W @ 120 VAC, 1200 W @ 240/277 VAC
Sensor Coverage Pattern	180 °	Sensor Type	Occupancy
Frequency Band	60 Hz	Operating Temperature Max	131 °F
Light Level Adjustment	8-180 fc	Number of Buttons	1
Sensor Technology	Dual Technology, Passive Infrared (PIR), Ultrasonic	Timer Duration	15 Minutes, 30 Minutes, 5 Minutes
Number of Poles	Multi-Location	Indicator	PIR Detection LED, Selectable audible alert for impending shutoff, Ultrasonic Detection LED
Input Voltage	120/277 VAC	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Sensor Coverage	1050 sq ft

Sensitivity Adjustment	PIR (Min/Max), Ultrasonic (0-100%)	Mounting Type	In-Wall
On Function	Selectable Auto/Manual	Operating Temperature	0°-55°C, 32°- 131°F
Operating Humidity	5-95% RH (Non- Condensing)	Sensing Range	Major motion: PIR 35x30 ft, Ultrasonic 20x20 ft,Minor motion: PIR 20 x 15 ft, Ultrasonic 15x15 ft
Location Rating	Dry	Wire Connection Type	Flying Leads
Storage Temperature	23° - 176° F, -5° - 80° C		