



Pass and Seymour  
Non-Fusible Mechanical Interlock  
Part No. PS360MIR4W



Double-Pole, Tamper-Resistant wire, Non-Fusible Mechanical Interlock Receptacle. 7 1/2 HP. 60A, 120VAC.

## Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007133486	Country Of Origin	United States

### Dimensions

Product Width US	6.88 in	Product Depth US	9.0 in
Product Height US	9.0 in		

### Technical Information

Amperage	60 A
----------	------