

400A 600V MALE CAM TYPE PLUG



Features & Benefits

Thermoplastic elastomer housing for outstanding impact and chemical resistance, as well as an exceptional seal for maintaining NEMA Type 3R and 4 integrity.

Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product.

Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity.

Heavy-duty hex set screws allow greater termination torque.

Specifications

General Info

Product Line	Pass & Seymour	Color	Blue
UPC Number	785007308082	Country Of Origin	Mexico
Features	Chemical Resistant	Application Sector	Commercial, Industrial
Standard	UL, cCSAus	Warranty Type	1-Year
Type	Connector		

Dimensions

Product Length US	6.875 in
-------------------	----------

Technical Information

Operating Temperature Min	-40 °C	Flanged	No
---------------------------	--------	---------	----

Terminal Accommodation	2/0 - 4/0	Operating Temperature Max	75 °C
Amperage	400 A	Number of Poles	Single Pole
Indoor/Outdoor	Indoor	Operating Temperature	-40°-75°C
Voltage	600.0 V	Environmental Conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4