



400A 600V M PLUG ORANGE #2-2/0

Features & Benefits

Thermoplastic elastomer housing for outstanding impact and chemical resistance, as well as an exceptional seal for maintaining NEMA Type 3R and 4 integrity.

Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity.

Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product.

Heavy-duty hex set screws allow greater termination torque.

Specifications

General Info

| | | | |
|--------------------|------------------------|-------------------|------------|
| Product Line | Pass & Seymour | Color | Red |
| UPC Number | 785007308020 | Country Of Origin | Mexico |
| Application Sector | Commercial, Industrial | Standard | UL, cCSAus |

Technical Information

| | | | |
|--------------------------|---|-----------------|-------------|
| Amperage | 400 A | Number of Poles | Single Pole |
| Wire Size | 2/0 | Voltage | 600.0 V |
| Environmental Conditions | Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4 | | |