



Pass and Seymour  
15A 125V Heavy Duty Spec-Grade Duplex Receptacle, Back and Side Wire, Ivory  
Part No. PS5262I



Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 15A 125V

## Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Strap tabs wrap around face to prevent strap from separating from face and back body.

High strength nylon face.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor	Application Sector	Commercial
Standard	cULus UL498, CSA C22.2 No. 42	Type	Outlet

### Dimensions

---

Product Width US 1.322 in

Product Depth US 0.78 in

---

Product Height US 2.635 in

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed Yes

---

### Technical Information

---

Dielectric Strength Withstands 2000V minimum

Connection Back and side wire

---

Number of Wires 3

Temperature Rating -40° - 60° C

---

Amperage 15 A

Number of Poles Double Pole

---

Wire Size 14 - 10 AWG

Indoor/Outdoor Indoor

---

Voltage 125.0 V

Environmental Conditions Flammability: UL94 V2

---