



Pass and Seymour
Non-Fusible Mechanical Interlock
Part No. PS360MIR4W



Double-Pole, Tamper-Resistant wire, Non-Fusible Mechanical Interlock Receptacle. 7 1/2 HP. 60A, 120VAC.

Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

Specifications

General Info

| | | | |
|-----------------------|----------------|--------------------|--------------------------|
| Product Line | Pass & Seymour | Color | Gray |
| UPC Number | 785007133486 | Country Of Origin | United States |
| Number of Receptacles | 1 | Features | Adjustable Mounting Feet |
| Outlet Type | Pin & Sleeve | Application Sector | Industrial |
| Wall Plate Included | Yes | Warranty Type | 1-Year |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 6.88 in | Product Depth US | 9.0 in |
| Product Height US | 9.0 in | | |

Technical Information

| | | | |
|---------------------------|------------------|---------------------------|------------------|
| Operating Temperature Min | -50 °C | Connection Location | Top and Bottom |
| Number of Wires | 3 | Operating Temperature Max | 60 °C |
| Amperage | 60 A | IEC Clock Position | Clock Position 4 |
| Enclosure Type | NEMA 12, NEMA 4X | Number of Poles | Double Pole |
| Indoor/Outdoor | Indoor | Operating Temperature | -50°-60°C |
| Wire Connection Type | Screw Terminals | Voltage | 120.0 V |