



400A 600V MALE CAM TYPE PLUG

Features & Benefits

Thermoplastic elastomer housing for outstanding impact and chemical resistance, as well as an exceptional seal for maintaining NEMA Type 3R and 4 integrity.

Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity.

Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product.

Heavy-duty hex set screws allow greater termination torque.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007308051	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Standard	UL, cCSAus

Dimensions

Product Length US	6.875 in
-------------------	----------

Technical Information

Amperage	400 A	Number of Poles	Single Pole
Wire Size	2/0 - 4/0	Voltage	600.0 V

Environmental Conditions

Operating Temperature: Maximum continuous
+75°C, minimum -40°C without impact:
Flammability UL94 V2: Enclosure: NEMA Type
3R and 4
