



Pass and Seymour
15A 125V Heavy Duty Spec-Grade Duplex Receptacle, Back and Side Wire, Red
Part No. PS5262RED



Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 15A 125V

Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

High strength nylon face.

Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

| | | | |
|-----------------------|--|--------------------|------------|
| Product Line | Pass & Seymour | Color | Red |
| UPC Number | 785007859904 | Country Of Origin | Mexico |
| Number of Receptacles | 2 | Application Sector | Commercial |
| Standard | cULus UL498, CSA C22.2 No. 42, FEDSPEC | Type | Outlet |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 1.322 in | Product Depth US | 0.78 in |
| Product Height US | 2.635 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|--------------------------|--------------------------|--------------------|--------------------|
| Dielectric Strength | Withstands 2000V minimum | Connection | Back and side wire |
| Number of Wires | 3 | Temperature Rating | -40° - 60° C |
| Amperage | 15 A | Number of Poles | Double Pole |
| Wire Size | 14 - 10 AWG | Indoor/Outdoor | Indoor |
| Environmental Conditions | Flammability: UL94 V2 | | |