



Pass and Seymour  
20A 125V Heavy Duty Spec-Grade Duplex Receptacle, Back and Side Wire, Black  
Part No. PS5362BK



Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 20A 125V

## Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Strap tabs wrap around face to prevent strap from separating from face and back body.

High strength nylon face.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

|                   |                               |                       |                         |
|-------------------|-------------------------------|-----------------------|-------------------------|
| Product Line      | Pass & Seymour                | Color                 | Black                   |
| Country Of Origin | Mexico                        | Number of Receptacles | 2                       |
| Outlet Type       | Commercial, Indoor            | Application Sector    | Commercial              |
| Standard          | cULus UL498, CSA C22.2 No. 42 | Warranty Type         | 1-Year Limited Warranty |
| Type              | Outlet                        |                       |                         |

### Dimensions

|                  |          |                  |         |
|------------------|----------|------------------|---------|
| Product Width US | 1.322 in | Product Depth US | 0.78 in |
|------------------|----------|------------------|---------|

---

Product Height US 2.635 in

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed Yes

---

### Technical Information

---

|                     |                          |                          |                       |
|---------------------|--------------------------|--------------------------|-----------------------|
| Dielectric Strength | Withstands 2000V minimum | Connection               | Back and side wire    |
| Number of Wires     | 3                        | Temperature Rating       | -40° - 60° C          |
| Amperage            | 20 A                     | Number of Poles          | Double Pole           |
| Wire Size           | 14 - 10 AWG              | Indoor/Outdoor           | Indoor                |
| Voltage             | 125.0 V                  | Environmental Conditions | Flammability: UL94 V2 |

---