



Pass and Seymour
20A 125V Heavy Duty Spec-Grade Duplex Receptacle, Back and Side Wire, Red
Part No. PS5362RED



Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 20A 125V

Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

High strength nylon face.

Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
UPC Number	785007859980	Country Of Origin	Mexico
Number of Receptacles	2	Application Sector	Commercial
Standard	cULus UL498, CSA C22.2 No. 42, FEDSPEC	Warranty Type	1-Year Limited Warranty

Type	Outlet		
Dimensions			
Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
Environmental Conditions	Flammability: UL94 V2		