



Pass and Seymour  
20A 125V Heavy Duty Hospital-Grade Duplex Receptacle, Back and Side Wire, Brown  
Part No. PS8300H



Heavy-Duty Hospital Grade Duplex Receptacle Back and Side Wire 20A 125V

## Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Two drive screws anchor strap to back body and face.

Tri-drive brass terminal screws.

Two back wire holes for more wiring flexibility.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

|                       |                                  |                    |                            |
|-----------------------|----------------------------------|--------------------|----------------------------|
| Product Line          | Pass & Seymour                   | Color              | Brown                      |
| UPC Number            | 785007860016                     | Country Of Origin  | United States              |
| Number of Receptacles | 2                                | Application Sector | Commercial, Hospital Grade |
| Standard              | UL498, CSA C22.2 No. 42, FEDSPEC | Type               | Outlet                     |

### Dimensions

|                  |          |                  |         |
|------------------|----------|------------------|---------|
| Product Width US | 1.322 in | Product Depth US | 0.78 in |
|------------------|----------|------------------|---------|

|                   |          |
|-------------------|----------|
| Product Height US | 2.635 in |
|-------------------|----------|

Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

|                     |                          |            |                    |
|---------------------|--------------------------|------------|--------------------|
| Dielectric Strength | Withstands 2000V minimum | Connection | Back and side wire |
|---------------------|--------------------------|------------|--------------------|

|                 |   |                    |              |
|-----------------|---|--------------------|--------------|
| Number of Wires | 3 | Temperature Rating | -40° - 60° C |
|-----------------|---|--------------------|--------------|

|          |      |                 |             |
|----------|------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

|           |             |                |        |
|-----------|-------------|----------------|--------|
| Wire Size | 14 - 10 AWG | Indoor/Outdoor | Indoor |
|-----------|-------------|----------------|--------|

|                          |                       |
|--------------------------|-----------------------|
| Environmental Conditions | Flammability: UL94 V2 |
|--------------------------|-----------------------|