



Pass and Seymour

Heavy-Duty Hospital Grade Receptacles, Back & Side Wire, 20A, 125V, Ivory
Part No. PS8300HI



Heavy-Duty Hospital Grade Duplex Receptacle Back & Side Wire 20amp 125volt White

Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Two drive screws anchor strap to back body and face.

Internal screw-pressure-plate back and side wire capability.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Tri-drive brass terminal screws.

Two back wire holes for more wiring flexibility.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color	Ivory	UPC Number	785007860023
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Poles	Double Pole	Voltage	125 V
Connection	Back and side wire	Dielectric Strength	Withstands 2000V minimum
Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact	Wire Size	#14 - #10

Number of
Wires 3

Environmental Conditions

Flammability: UL94 V2
