



Pass and Seymour
15A NEMA L615 Plug - Black Back, White Front Body
Part No. PSL615P

15A 250V Extra-hard Use (ehu) Turnlok® Back Front Body



Features & Benefits

| | |
|---|--|
| Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire. | Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity. |
| Raised ribs provide non-slip gripping profile for turning to lock and unlock. | Double dovetail design provides superior protection against cord pull-out forces. |
| Impact- and corrosion-resistant durable nylon 6/6 shell material. | Rounded back contour reduces snags and hang-ups on the job site. |
| Scallop shell design provides non-slip gripping surface for insertion and withdrawal. | Visible stamped NEMA configuration and device rating. |
| New-design external cord grips provide visible assurance of safe and proper cord retention. | Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber. |

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Black |
| Country Of Origin | Mexico | Application Sector | Industrial |
| Standard | UL 498 | | |

Dimensions

| | | | |
|-------------------|----------|-------------------|----------|
| Product Height US | 1.358 in | Product Length US | 2.617 in |
|-------------------|----------|-------------------|----------|

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|-----------------|---|----------|------|
| Number of Wires | 3 | Amperage | 15 A |
|-----------------|---|----------|------|

| | | | |
|-----------------|-------------|-----------|---|
| Number of Poles | Double Pole | Wire Size | 4 |
|-----------------|-------------|-----------|---|

| | |
|---------|---------|
| Voltage | 250.0 V |
|---------|---------|