



20A GFCI works with the existing three-wire PlugTail connectors creating a non-feed thru application for facility owners. At rough-in, just install the same right-angle connector for GFCI and receptacle openings. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

| | |
|--|---|
| Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock® Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected | Faster, more reliable installation |
| No exposed terminals create a finger-safe application before, during, and after installation | Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector |
| GFCI works with the existing 3-wire PlugTail connectors creating a non-feed-through application for facility | Zinc-plated steel mounting strap |

Specifications

General Info

| | | | |
|-------------------|-------------------------------------|-----------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Red |
| Country Of Origin | China | Number of Receptacles | 2 |
| Outlet Type | Commercial, GFCI, Indoor, Self-Test | Application Sector | Residential/Commercial |
| Standard | cULus, UL Listed, FSUL | Warranty Type | 1-Year Limited Warranty |
| Type | Outlet | | |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 1.72 in | Product Depth US | 1.2 in |
| Product Height US | 4.2 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|------------------|-----|------------------|-------|
| Interrupt Rating | 4 A | Frequency Rating | 60 Hz |
|------------------|-----|------------------|-------|

| | | | |
|------------|--------|------------|--------------------|
| Trip Range | 5±1 mA | Connection | Built-in Connector |
|------------|--------|------------|--------------------|

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | | | |
|----------------|--------|---------|---------|
| Indoor/Outdoor | Indoor | Voltage | 125.0 V |
|----------------|--------|---------|---------|

| | | | |
|--------------------------|------------------------|--|--|
| Environmental Conditions | 95% Humidity, UL 94 V2 | | |
|--------------------------|------------------------|--|--|
