




## radiant Collection

**radiant® Tamper-Resistant 20A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, North American-Compliant, White**  
Part No. PT2097TRNAW



PlugTail® Spec-Grade Tamper-Resistant 20A Self-Test Duplex GFCI. Self-test GFCI Technology - conducts an automatic test every three seconds, ensuring it's always ready to protect. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

The indicator light flashes if the device fails the self-test, signalling that the GFCI should be replaced. Tamper-resistant automatic shutter system prevents young children from inserting common household objects.

High-impact-resistant, thermoplastic construction for superior strength and durability

GFCI works with the existing three-wire PlugTail connectors creating a non-feed thru application for facility owners. At rough-in, just install the same right-angle connector for GFCI and receptacle openings.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007052794	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	GFCI, Self-Test, Tamper-Resistant
Application Sector	Commercial	Standard	cULus, UL Listed, FSUL
Warranty Type	1-Year Limited Warranty		

### Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
Product Height US	4.2 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Is Tamper-Resistant	Yes	Connection	Built-in Connector
Number of Gangs	1	Amperage	20 A
Indoor/Outdoor	Indoor	Mounting Type	Box

---

Environmental Conditions	95% Humidity, UL 94 V2
--------------------------	------------------------

---