



20A GFCI works with the existing three-wire PlugTail connectors creating a non-feed thru application for facility owners. At rough-in, just install the same right-angle connector for GFCI and receptacle openings. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

## Features & Benefits

- Conducts an automatic test every three seconds, ensuring it's always ready to SafeLock® Protection feature: if critical protect. If the device fails the test, the indicator light flashes to signal that the components are damaged and protection is lost, GFCI should be replaced. It also has our proven
- Faster, more reliable installation
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector
- Zinc-plated steel mounting strap
- power to the receptacle is disconnected
- No exposed terminals create a finger-safe application before, during, and after installation
- GFCI works with the existing 3-wire PlugTail connectors creating a non-feed-through application for facility

## Specifications

General Info			
Product Line	Pass & Seymour	Color	Red
UPC Number	785007047899	Country Of Origin	China
Number of Receptacles	2	Outlet Type	GFCI, Self-Test
Application Sector	Commercial	Standard	cULus, UL Listed, FSUL
Warranty Type	1-Year Limited Warranty	Type	Outlet
Dimensions			
Product Width US	1.72 in	Product Depth US	1.2 in
Product Height US	4.2 in		

---

Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

Technical Information

---

Connection	Built-in Connector	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Environmental Conditions	95% Humidity, UL 94 V2		

---