



Plugtail Heavy-Duty Spec Grade Single Receptacles with Side and Back Wire install 5x faster than conventional wiring devices.

In the world of commercial wiring device installation, it's all about flexibility. For years now, PlugTail® electrical wiring devices have been providing that flexibility in commercial buildings everywhere. Easy to install, change out and upgrade, PlugTail allows you to continuously reconfigure to meet a building's electrical requirements as the space transforms – without the time and expense of rewiring. It's a cost-effective, code-compliant, proven way to keep your customers connected to the future, while securing your reputation as a forward-thinking electrical contractor.

Features & Benefits

PlugTail Devices install up to 5 times faster than traditional devices. No exposed terminals create a finger-safe application before, during and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections. Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger-safe housing.

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly. Impact-resistant nylon face and thermoplastic back body.

Tri-drive terminal and mounting screws. Auto-ground clip assures positive ground.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Glossy	Country Of Origin	Mexico
Receptacle Type	Straight Blade	Number of Receptacles	1
Outlet Type	Commercial	Package Quantity	1
Application Sector	Commercial	Standard	UL UL498, CSA No.C22.2
Warranty Type	1-Year Limited Warranty	Type	Outlet, Plug Tail, Single

Dimensions

Product Width US	1.546 in	Product Depth US	1.9 in
------------------	----------	------------------	--------

Product Height US 4.185 in

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Amperage	15 A	Indoor/Outdoor	Indoor
----------	------	----------------	--------

Voltage	125.0 V	Environmental Conditions	95% (relative humidity, non-condensing)
---------	---------	--------------------------	---
