



PlugTail® Spec Grade Receptacles, 15A, 125V PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Illuminated face indicates power to receptacle and makes it easy to identify receptacle in dark applications.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Crimped and welded contacts.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007091571	Country Of Origin	Mexico
Number of Receptacles	2	Application Sector	Commercial

Standard	UL 498, FEDSPEC	Type	Outlet
----------	-----------------	------	--------

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes		
--------------	-----	--	--

Technical Information

Phase	Three	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor