



Pass and Seymour  
**PlugTail® 20A 125V Spec-Grade Duplex Receptacle, Blue**  
Part No. PT5362BL



PlugTail® Spec Grade Receptacles, 20A, 125V PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Plated steel wrap strap design for maximum durability and corrosion resistance.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Crimped and welded contacts.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

## Specifications

### General Info

|                   |                    |                       |                         |
|-------------------|--------------------|-----------------------|-------------------------|
| Product Line      | Pass & Seymour     | Color                 | Blue                    |
| Country Of Origin | Mexico             | Number of Receptacles | 2                       |
| Outlet Type       | Commercial, Indoor | Warranty Type         | 1-Year Limited Warranty |

|      |        |
|------|--------|
| Type | Outlet |
|------|--------|

Dimensions

|                   |         |                  |          |
|-------------------|---------|------------------|----------|
| Product Width US  | 1.5 in  | Product Depth US | 0.625 in |
| Product Height US | 2.75 in |                  |          |

Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

|                |        |                 |             |
|----------------|--------|-----------------|-------------|
| Amperage       | 20 A   | Number of Poles | Double Pole |
| Indoor/Outdoor | Indoor | Voltage         | 125.0 V     |