



Pass and Seymour  
**PlugTail® 20A 125V Spec-Grade Duplex Receptacle, Light Almond**  
Part No. PT5362LA



PlugTail® Spec Grade Receptacles, 20A, 125V PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Plated steel wrap strap design for maximum durability and corrosion resistance.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Crimped and welded contacts.

Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Commercial, Indoor
Application Sector	Commercial	Standard	cULus UL498

---

Warranty Type	1-Year Limited Warranty	Type	Outlet
---------------	-------------------------	------	--------

---

### Dimensions

---

Product Width US	1.5 in	Product Depth US	0.625 in
------------------	--------	------------------	----------

---

Product Height US	2.75 in
-------------------	---------

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

### Technical Information

---

Dielectric Strength	Withstands 2000V minimum	Number of Wires	3
---------------------	--------------------------	-----------------	---

---

Temperature Rating	-40° - 60° C	Amperage	20 A
--------------------	--------------	----------	------

---

Number of Poles	Double Pole	Wire Size	12 AWG
-----------------	-------------	-----------	--------

---

Indoor/Outdoor	Indoor	Voltage	125.0 V
----------------	--------	---------	---------

---

Environmental Conditions	Flammability: UL94 V2
--------------------------	-----------------------

---