



PlugTail® Split Circuit Spec Grade Receptacles, 20A, 125A

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Large brass contacts snugly terminate on device blade terminals.

Pre-wired with one welded pre-stripped wire lead to facilitate switched receptacle circuit applications.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Plated steel wrap strap design for maximum durability and corrosion resistance.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Crimped and welded contacts.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007000160
Country Of Origin	Mexico	Application Sector	Commercial

Standard	cULus UL498, FEDSPEC
----------	----------------------

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Number of Wires	3
Temperature Rating	-40° - 60° C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	12 AWG
Environmental Conditions	Flammability: UL94 V2		