



Pass and Seymour
PlugTail® Tamper-Resistant Hospital Grade Receptacle, 15A, 125V, Red
Part No. PTTR26262HGRED



PlugTail® Tamper-Resistant Hospital Grade Decorator Receptacle, 15 A 125 V, White. For detailed PlugTail® information, visit our PlugTail® Headquarters. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

- Dual mechanical shutter system to help prevent insertion of foreign objects
 - Plated steel wrap strap design for maximum durability and corrosion resistance.
 - Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
 - Pre-stripped connector leads fasten to conductors, easier than standard pigtailed
 - For covering patents, see www.legrand.us/patents.
 - Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
 - No exposed terminals create a finger safe application before, during, and after installation.
 - Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
 - Auto-ground clip assures positive ground.
 - For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).
 - PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Country Of Origin	Mexico	Application Sector	Commercial
Standard	cULus UL498		

Dimensions

Product Width US	1.5 in	Product Depth US	0.875 in
Product Height US	2.6 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	12 AWG	Voltage	125.0 V
Environmental Conditions	Flammability: UL94 V2		
