



Pass and Seymour
PlugTail® 20A 125V Hospital-Grade Tamper-Resistant Decorator Duplex Receptacle,, Ivory
 Part No. PTTR26362HGI



PlugTail® Tamper-Resistant Hospital Grade Decorator Receptacle, 20A 125V. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

- Dual mechanical shutter system to help prevent insertion of foreign objects
 - Plated steel wrap strap design for maximum durability and corrosion resistance.
 - Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
 - Auto-ground clip assures positive ground.
 - For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).
- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
 - No exposed terminals create a finger safe application before, during, and after installation.
 - Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
 - For covering patents, see www.legrand.us/patents.
 - Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
 - Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor, Tamper-Resistant	Application Sector	Commercial
Standard	cULus UL498	Type	Outlet

Dimensions

Product Width US	1.5 in	Product Depth US	0.875 in
------------------	--------	------------------	----------

Product Height US	2.75 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
---------------------	--------------------------	---------------------	-----

Number of Wires	3	Temperature Rating	-40° - 60° C
-----------------	---	--------------------	--------------

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	12 AWG	Indoor/Outdoor	Indoor
-----------	--------	----------------	--------

Voltage	125.0 V	Environmental Conditions	Flammability: UL94 V2
---------	---------	--------------------------	-----------------------
