



PlugTail® Extra Heavy-Duty Hospital Grade Illuminated Receptacles, 20A, 125V PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

Molded-in "IL" markings on face of product.	Efficient, 15.5W power supply for fast charging of mobile phones and tablets
Exclusive patented feature, circuit label on face allows permanent circuit identification.	.036 inch thick, brass, triple-wipe power contacts for lasting retention.
Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.	No exposed terminals create a finger safe application before, during, and after installation.
Crimped and welded contacts.	Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
Large brass contacts snugly terminate on device blade terminals.	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only	

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007238532	Country Of Origin	Mexico
Number of Receptacles	2	Features	Nightlight
Application Sector	Commercial, Hospital Grade	Standard	cULus UL498, FEDSPEC
Type	Outlet		

Dimensions

Product Width US	1.625 in	Product Depth US	0.856 in
Product Height US	2.75 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Number of Wires	3
Temperature Rating	-40° - 60° C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	12 AWG
Indoor/Outdoor	Indoor	Environmental Conditions	Flammability: UL94 V2