



Pass and Seymour

**PlugTail® Tamper-Resistant Heavy Duty Spec Grade Plug Load Controllable Receptacle, 15A, 125V, Light Almond**  
Part No. PTTR5262CDLA



These durable, dependable receptacles feature a permanently marked, differentiated solution that meets all necessary code requirements. For detailed PlugTail® information, visit our PlugTail® Headquarters. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Plated steel wrap strap design for maximum durability and corrosion resistance.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Dual mechanical shutter system to help prevent insertion of foreign objects (TR models).

Permanent controlled markings on face of receptacle compliant with ASHRAE 90.1, CA Title 24, and NEC.

Auto-ground clip assures positive ground.

Half-controlled versions include welded, pre-wired lead that control top half of receptacle for split circuit applications.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Wire Size: #12 AWG THHN

## Specifications

### General Info

|              |                |       |              |
|--------------|----------------|-------|--------------|
| Product Line | Pass & Seymour | Color | Light Almond |
|--------------|----------------|-------|--------------|

|                   |        |                    |            |
|-------------------|--------|--------------------|------------|
| Country Of Origin | Mexico | Application Sector | Commercial |
|-------------------|--------|--------------------|------------|

|          |                             |
|----------|-----------------------------|
| Standard | UL Listed, CSA Listed, FSUL |
|----------|-----------------------------|

### Dimensions

|                  |          |                  |         |
|------------------|----------|------------------|---------|
| Product Width US | 1.322 in | Product Depth US | 0.78 in |
|------------------|----------|------------------|---------|

|                   |          |
|-------------------|----------|
| Product Height US | 2.635 in |
|-------------------|----------|

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

### Technical Information

|                     |                          |                     |     |
|---------------------|--------------------------|---------------------|-----|
| Dielectric Strength | Withstands 2000V minimum | Is Tamper-Resistant | Yes |
|---------------------|--------------------------|---------------------|-----|

---

|                          |         |                    |              |
|--------------------------|---------|--------------------|--------------|
| Phase                    | Single  | Connection         | PlugTail     |
| Number of Wires          | 3       | Temperature Rating | -40° - 60° C |
| Amperage                 | 15 A    | Number of Poles    | Double Pole  |
| Wire Size                | 12 AWG  | Voltage            | 125.0 V      |
| Environmental Conditions | UL94 V2 |                    |              |

---