



PlugTail® Tamper-Resistant Spec Grade Receptacles, 15A, 125V PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Receptacle compliant with 2014 NEC, CA Title 24, and ASHRAE 90.1

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Crimped and welded contacts.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Pre-wired with one welded pre-stripped wire lead to facilitate switched receptacle circuit applications.

Auto-ground clip assures positive ground.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

## Specifications

### General Info

|                       |                |                   |                                      |
|-----------------------|----------------|-------------------|--------------------------------------|
| Product Line          | Pass & Seymour | Country Of Origin | Mexico                               |
| Number of Receptacles | 2              | Outlet Type       | Commercial, Indoor, Tamper-Resistant |
| Application Sector    | Commercial     | Standard          | UL 498                               |

---

|      |        |
|------|--------|
| Type | Outlet |
|------|--------|

---

### Dimensions

---

|                  |        |                  |          |
|------------------|--------|------------------|----------|
| Product Width US | 1.5 in | Product Depth US | 0.625 in |
|------------------|--------|------------------|----------|

---

|                   |         |
|-------------------|---------|
| Product Height US | 2.75 in |
|-------------------|---------|

---

### Listing Agencies / 3rd Party Agencies

---

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

---

### Technical Information

---

|                     |     |       |   |
|---------------------|-----|-------|---|
| Is Tamper-Resistant | Yes | Phase | 3 |
|---------------------|-----|-------|---|

---

|                 |   |          |      |
|-----------------|---|----------|------|
| Number of Wires | 3 | Amperage | 15 A |
|-----------------|---|----------|------|

---

|                 |             |           |             |
|-----------------|-------------|-----------|-------------|
| Number of Poles | Double Pole | Wire Size | 14 - 10 AWG |
|-----------------|-------------|-----------|-------------|

---

|                |        |         |         |
|----------------|--------|---------|---------|
| Indoor/Outdoor | Indoor | Voltage | 125.0 V |
|----------------|--------|---------|---------|

---