



PlugTail® Isolated Ground Spec Grade Receptacles, 15A, 125A

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Crimped and welded contacts.

Large brass contacts snugly terminate on device blade terminals.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Plated steel wrap strap design for maximum durability and corrosion resistance.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                    |                |                   |        |
|--------------------|----------------|-------------------|--------|
| Product Line       | Pass & Seymour | Country Of Origin | Mexico |
| Application Sector | Commercial     | Standard          | UL 498 |

### Dimensions

|                  |        |                  |          |
|------------------|--------|------------------|----------|
| Product Width US | 1.5 in | Product Depth US | 0.625 in |
|------------------|--------|------------------|----------|

|                   |         |
|-------------------|---------|
| Product Height US | 2.75 in |
|-------------------|---------|

Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

|       |   |                 |   |
|-------|---|-----------------|---|
| Phase | 3 | Number of Wires | 3 |
|-------|---|-----------------|---|

|          |      |                 |             |
|----------|------|-----------------|-------------|
| Amperage | 15 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

|           |             |         |         |
|-----------|-------------|---------|---------|
| Wire Size | 14 - 10 AWG | Voltage | 125.0 V |
|-----------|-------------|---------|---------|