



Pass and Seymour

PlugTail® 20A 125V Extra Heavy Duty Hospital-Grade Tamper-Resistant Duplex Receptacle, Red
Part No. PTTR63HRED



PlugTail® Extra Heavy-Duty Hospital Grade Tamper-Resistant Receptacles, 20A, 125V
PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Crimped and welded contacts.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see www.legrand.us/patents.

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Auto-ground clip assures positive ground.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

| | | | |
|-----------------------|----------------|-------------------|--------------------------------------|
| Product Line | Pass & Seymour | Color | Red |
| Finish | Matte | Country Of Origin | Mexico |
| Number of Receptacles | 2 | Outlet Type | Commercial, Indoor, Tamper-Resistant |

| | | | |
|--|--------------------------|---------------------|-------------|
| Application Sector | Commercial | Standard | cULus UL498 |
| Type | Outlet | | |
| Dimensions | | | |
| Product Width US | 1.625 in | Product Depth US | 0.9 in |
| Product Height US | 3.281 in | | |
| Listing Agencies / 3rd Party Agencies | | | |
| cULus ListingNumber | 140596 | cULus Listed | Yes |
| Technical Information | | | |
| Dielectric Strength | Withstands 2000V minimum | Is Tamper-Resistant | Yes |
| Temperature Rating | -40° - 60° C | Amperage | 20 A |
| Number of Poles | Double Pole | Wire Size | 12 AWG |
| Indoor/Outdoor | Indoor | Voltage | 125.0 V |