



Pass and Seymour  
PlugTail® Hospital Grade Tamper-Resistant Surge Protective Duplex Receptacle, Red  
Part No. PTTR8200REDSP



PlugTail information, visit our PlugTail Headquarters. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.	Plated steel wrap strap design for maximum durability and corrosion resistance.
No exposed terminals create a finger safe application before, during, and after installation.	Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
Crimped and welded contacts.	Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
Large brass contacts snugly terminate on device blade terminals.	Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.
Auto-ground clip assures positive ground.	For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007020427
Country Of Origin	China	Application Sector	Commercial, Residential
Standard	CSA Listed, cUL, UL Listed, RoHS, FSUL		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Phase	Single	Connection	Built-in Connector
Class	IG	Amperage	15 A
Type of Indicators	Audible Alarm, LED	Environmental Conditions	UL94 V2