



Pass and Seymour

PlugTail® 20A 125V Hospital-Grade Tamper-Resistant Duplex Receptacle, Back and Side Wire, Gray

Part No. PTTR8300GRY



PlugTail® Tamper-Resistant Hospital Grade Duplex Receptacle, Back and Side Wire, 20A, 125V. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects
Brushed finish.

Plated steel wrap strap design for maximum durability and corrosion resistance.
No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Auto-ground clip assures positive ground.
For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).
Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Commercial, Indoor, Tamper-Resistant
Application Sector	Commercial	Standard	UL 498

Type	Outlet
------	--------

Dimensions

Product Width US	1.5 in	Product Depth US	0.625 in
------------------	--------	------------------	----------

Product Height US	3.281 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Amperage	20 A
---------------------	-----	----------	------

Number of Poles	Double Pole	Wire Size	14 - 10 AWG
-----------------	-------------	-----------	-------------

Indoor/Outdoor	Indoor	Voltage	125.0 V
----------------	--------	---------	---------
